



**Big ergonomic brush - White - Medium bristle**

Ergonomic brush ideal for cleaning all surfaces.



Code	Colour	Size (mm)	Material	Bristle (mm)	Bristle height (mm)	Net weight (kg)
<b>1001WM</b>	White	230 x 100 x 55	PP - PBT	Medium - Ø 0,5	35	0,24

**Usage information**

Minimum and maximum temperature	min -20 / max 80 C°
Washing (dishwasher)	80° C for 8 min (recommended)
Autoclave	121° C for 20 min
User and maintenance manual	<ul style="list-style-type: none"> <li>- Remove packaging and any label from tools and disinfect them.</li> <li>- Both manual and autoclave disinfection is possible.</li> <li>- Sanitize tools using appropriate chemical decontamination products, in the concentrations, times and temperatures provided.</li> <li>- Make sure tools completely dry up before next use.</li> <li>- Hang tools while drying up to avoid any contamination, breakage or bristles distortion.</li> <li>- The storing area must be clean and far away from sources of intense light or heat.</li> <li>- Do not use damaged tools, both supports and bristles must be in a good state.</li> </ul>

**Compliance**

- REACH
- FDA
- EU 1935/2004 and updates
- EU 2023/2006 and updates
- EU 10/2011 and updates

**Logistical information**

Internal packaging type	Poly bag	Product barcode	8008805101429
External packaging type	Carton	Box barcode	08008805101429
Quantity per pack (pcs)	6	Customs tariff	96039091
Box gross weight (kg)	1,68	Country of origin	Italy
Box dimensions (mm)	280 x 230 x 130	Palletising (pcs)	840
Box volume (m³)	0,008372	Pallet dimensions (cm)	120 x 80 x 144,5

**Available versions**

Size		Bristle type	Tough - Ø 0,75
Colour	<span style="background-color: #00AEEF; border-radius: 50%; padding: 2px 5px;">B</span> <span style="background-color: #C00000; border-radius: 50%; padding: 2px 5px;">R</span> <span style="background-color: #FFD700; border-radius: 50%; padding: 2px 5px;">Y</span> <span style="background-color: #008000; border-radius: 50%; padding: 2px 5px;">G</span> <span style="background-color: #FF4500; border-radius: 50%; padding: 2px 5px;">O</span>	Material	Detectable