

## TECHNICAL DATA SHEET

Issue date: 06/11/23









## Push broom 45 cm - Orange - Medium bristle

Push broom, very resistant, for deeper and more effective cleaning. Universal connection suitable for all main thread types (ITA-FRA-GER-USA) and equipped with ring nut for handles Ø 21-25 mm



| Code   | Colour | Size (mm)      | Material | Bristle (mm)   | Bristle height (mm) | Thread    | Net weight (kg) |
|--------|--------|----------------|----------|----------------|---------------------|-----------|-----------------|
| 10090M | Orange | 480 x 80 x 185 | PP - PBT | Medium - Ø 0,5 | 80                  | Universal | 0,75            |

| Usage information               |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |  |  |  |  |
|---------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--|--|--|
| Minimum and maximum temperature | min -20 / max 80 C°                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |  |  |  |  |
| Washing (dishwasher)            | -                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |  |  |  |  |
| Autoclave                       | 121° C for 20 min                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |  |  |  |  |
| User and maintenance manual     | <ul> <li>Remove packaging and any label from tools and disinfect them.</li> <li>Both manual and autoclave disinfection is possible.</li> <li>Sanitize tools using appropriate chemical decontamination products, in the concentrations, times and temperatures provided.</li> <li>Make sure tools completely dry up before next use.</li> <li>Hang tools while drying up to avoid any contamination, breakage or bristles distortion.</li> <li>The storing area must be clean and far away from sources of intense light or heat.</li> <li>Do not use damaged tools, both supports and bristles must be in a good state.</li> </ul> |  |  |  |  |

## Compliance

- REACH
- FDA
- EU 1935/2004 and updates
- EU 2023/2006 and updates
- EU 10/2011 and updates

| Logistical information    |                 |                        |                  |  |  |  |
|---------------------------|-----------------|------------------------|------------------|--|--|--|
| Internal packaging type   | Poly bag        | Product barcode        | 8008805116720    |  |  |  |
| External packaging type   | Carton          | Box barcode            | 08008805116720   |  |  |  |
| Quantity per pack (pcs) 3 |                 | Customs tariff         | 96039091         |  |  |  |
| Box gross weight (kg)     | 2,64            | Country of origin      | Italy            |  |  |  |
| Box dimensions (mm)       | 500 x 210 x 175 | Palletising (pcs)      | 162              |  |  |  |
| Box volume (m³)           | 0,018375        | Pallet dimensions (cm) | 124 x 88 x 119,5 |  |  |  |

| Available versions |                   |              |            |  |  |
|--------------------|-------------------|--------------|------------|--|--|
| Size               | Cod. 1038 (30 cm) | Bristle type |            |  |  |
| Colour             | B R Y G W         | Material     | Detectable |  |  |

## www.igeax.com