



### Detectable hand scraper 110 mm - Dark Blue

One piece polypropylene scraper for scraping off encrusted residues without damaging surfaces.



| Code          | Colour    | Size (mm)      | Material | Net weight (kg) |
|---------------|-----------|----------------|----------|-----------------|
| <b>1110BD</b> | Dark Blue | 110 x 250 x 20 | DPP      | 0,09            |

### Usage information

|                                 |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
|---------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Minimum and maximum temperature | min -20 / max 80 C°                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| Washing (dishwasher)            | -                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
| Autoclave                       | -                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
| User and maintenance manual     | <ul style="list-style-type: none"> <li>- Remove packaging and any label from tools and disinfect them.</li> <li>- Both manual and autoclave disinfection is possible.</li> <li>- Sanitize tools using appropriate chemical decontamination products, in the concentrations, times and temperatures provided.</li> <li>- Make sure tools completely dry up before next use.</li> <li>- Hang tools while drying up to avoid any contamination or breakage.</li> <li>- The storing area must be clean and far away from sources of intense light or heat.</li> <li>- Do not use damaged tools.</li> </ul> |

### Compliance

- REACH
- FDA
- EU 1935/2004 and updates
- EU 2023/2006 and updates
- EU 10/2011 and updates

### Logistical information

|                         |                |                        |                  |
|-------------------------|----------------|------------------------|------------------|
| Internal packaging type | Poly bag       | Product barcode        | 8008805101900    |
| External packaging type | Carton         | Box barcode            | 08008805101900   |
| Quantity per pack (pcs) | 12             | Customs tariff         | 39269099         |
| Box gross weight (kg)   | 1,2            | Country of origin      | United Kingdom   |
| Box dimensions (mm)     | 280 x 260 x 77 | Palletising (pcs)      | 2304             |
| Box volume (m³)         | 0,0056056      | Pallet dimensions (cm) | 120 x 80 x 137,7 |

### Available versions

|        |                     |          |    |
|--------|---------------------|----------|----|
| Size   | Cod. 1109BD (75 mm) | Material | PP |
| Colour |                     |          |    |